

RMG-12MPODQ4

RMG Fiber Optic Module, 12-fiber, MPO-LC, Multimode, OM3, aqua

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	RMG

General Specifications

Functionality	Breakout
Application	For use with RMG panels
Adapter Color	Aqua
Adapters, quantity, front	3
Adapters, quantity, rear	1
Body Style	Quad Straight orientation
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Standard
Total Ports, quantity, front	12

Dimensions

Height	28.45 mm 1.12 in
Width	129.03 mm 5.08 in
Depth	115.82 mm 4.56 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM3

RMG-12MPODQ4

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

