



High-Density Front-Loading Cable Manager Shallow, 15U

- Offers bend radius and mechanical protection
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords
- Suitable for Twisted Pair and Fiber Optic patch cords

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Cable management hardware
Minimum Order Quantity	2
Ordering Note	Sold per piece with an MOQ of 2 pieces

General Specifications

Color	Black
Rack Units	15

Dimensions

Height	26.25 in 666.75 mm
Width	2.5 in 63.5 mm
Depth	3.86 in 98.044 mm

Material Specifications

Finish	Smooth
Material Type	Galvanized steel PA TPE

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant

UK-ROHS

Compliant

