

48939A-2



Boot Assembly, 5 in, for 7/8 in corrugated coaxial cable

Product Classification

Product Type	Boot assembly
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Cables per Cushion	3
Color	Black

Dimensions

Height	127 mm 5 in
Length	76.2 mm 3 in
Nominal Size	7/8 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packaging and Weights

Height, packed	190.5 mm 7.5 in
Width, packed	170.18 mm 6.7 in
Length, packed	78.74 mm 3.1 in
Included	Boot Cushion Two clamps
Packaging quantity	1

48939A-2

Weight, gross

0.9 kg | 1.984 lb

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant