



SnapSeal™ Entry Cushion with 1 hole for 1-1/4 in corrugated coaxial cable

Product Classification

| | |
|----------------------|---------------------------------|
| Product Type | Entry cushion |
| Ordering Note | CommScope® non-standard product |

General Specifications

| | |
|---------------------------|------------|
| Cable Type | Corrugated |
| Cables per Cushion | 1 |
| Color | Black |

Dimensions

| | |
|---------------------|--------------------|
| Height | 101.6 mm 4 in |
| Length | 31.75 mm 1.25 in |
| Nominal Size | 1-1/4 in |

Material Specifications

| | |
|----------------------|-------------------------------|
| Material Type | Thermoplastic elastomer (TPE) |
|----------------------|-------------------------------|

Environmental Specifications

| | |
|---|--|
| UV Resistance Test Method | MIL-STD-810E, Procedure 11, Method 505 |
| UV Resistance, minimum with no degradation | ≥1000 hours |

Packaging and Weights

| | |
|---------------------------|--|
| Height, packed | 170.18 mm 6.7 in |
| Width, packed | 129.54 mm 5.1 in |
| Length, packed | 99.06 mm 3.9 in |
| Included | Compression ring SnapSeal™ entry cushion |
| Packaging quantity | 1 |
| Weight, gross | 0.8 kg 1.764 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

