



ION-M4 U DC AI 380-385 390-395 High Power Remote Unit for TETRA Applications

Product Classification

Product Type	Remote unit
Product Brand	ION®-M

General Specifications

Minimum Software Requirement	ION-M SW V8.10.0
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	High

Electrical Specifications

Impedance	50 ohm
License Band	TETRA
Voltage Range	+36 to +60 Vdc

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	380 – 385 MHz
Wavelength	1550 nm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	390 – 395 MHz
---------------------------------	---------------