


# BLK-RCT-A03B0

---



Fiber Optic Ribbon Breakout Kit, 1-12F/ribbon, 12-96F/tube, 5-8 mm central tube outside dia., 3 tubes/leg

## Product Classification

|                              |                                 |
|------------------------------|---------------------------------|
| <b>Regional Availability</b> | Latin America   North America   |
| <b>Product Type</b>          | Fiber breakout kit, rectangular |
| <b>Product Series</b>        | BLK-R                           |

## General Specifications

|                                   |                                  |
|-----------------------------------|----------------------------------|
| <b>Application</b>                | For use with ribbon fiber cables |
| <b>Breakout Legs, quantity</b>    | 1                                |
| <b>Fibers per Ribbon, maximum</b> | 12                               |
| <b>Fibers per Tube, maximum</b>   | 108                              |
| <b>Tube Type</b>                  | Ribbon central tube              |
| <b>Tubes per Leg, quantity</b>    | 3                                |

## Dimensions

|                                    |                                 |
|------------------------------------|---------------------------------|
| <b>Tube Length</b>                 | 5,001.26 mm   196.9 in          |
| <b>Central Tube Outer Diameter</b> | 5 mm – 8 mm (0.20 in – 0.33 in) |

## Environmental Specifications

|                            |         |
|----------------------------|---------|
| <b>Environmental Space</b> | Outdoor |
|----------------------------|---------|

## Packaging and Weights

|                           |              |
|---------------------------|--------------|
| <b>Packaging quantity</b> | 1            |
| <b>Packaging Type</b>     | Bag   Carton |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |

# BLK-RCT-A03B0

---

ROHS

Compliant

UK-ROHS

Compliant

