

760252850 | 20" Integrated Pole, 10' Tall Base



Round 20 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Pole top concealment module for LAA/CBRS radio mounting
- Concealment integrates AC load center/OVP and disconnect

Radio Bracket Mounting Kits ordered separately:

- MTM1160-1101-AMK-E – Ericsson Radio Bracket Kit
- MTM1160-1101-AMK-N – Nokia Radio Bracket Kit
- MTM1160-1101-AMK-S – Samsung Radio Bracket Kit

Product Classification

Portfolio	CommScope®
Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERG
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022)
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI
Cooling	Fan Cooling
Power Supply Compatibility	6304 ABB CC1600 CCI PSU-1200W-48-N DELTA 2.0 DELTA 3.0 PSU-AC-08
Radio Compatibility, Ericsson	1281 220x 440x 4415 4426 4449 6701 6705 8843 8863 Diplexer Distribution

760252850 | 20" Integrated Pole, 10' Tall Base

Radio Compatibility, Nokia	AHFIA AHFIB AHFIC AHIA AHIB AWHHF AWHQN AZRB Airscale micro Diplexer Power Distribution
Radio Compatibility Samsung	AT1K01 AT1K02 DELTA 2.0 Diplexer Power Distribution RF4402D-D1A RT2201-46A RT4401-48A
Radios Included	None

Dimensions

Height	3,048 mm 120 in
Height Note	10 ft tall Equipment Base
Pole Height Options	10.668 m 35 ft 12.192 m 40 ft 6.096 m 20 ft 7.62 m 25 ft 9.144 m 30 ft
Width	508 mm 20 in
Depth	508 mm 20 in
Depth Note	Round
Pole Diameter	203.2 mm 8 in

Electrical Specifications

Power/Fiber Input	AC load center with OVP and disconnect
--------------------------	--

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Pole Height Options	Overall AGL Standard Height