

# SSC-760249586X1 | Radio Enclosure MV2



## Future Ready Middle of the Pole Concealment for Samsung, Nokia, and Ericsson equipment

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760249586E1x Ericsson  
SSC-760249586N1x Nokia  
SSC-760249586S1x Samsung  
\*"X" is placeholder for color

Includes mounting hardware for clamp on, through-bolt, or banding to poles or structures.

Available After Market Kits -- ordered separately:

- 860661823S-xx Wood Pole 5" Standoff
- 860661823ST-xx Round Tapered Pole 5" Standoff
- 860661736-MV2-C01x Ice Canopy
- 860661736-MV2-C02 Delta 3.0 rectifier mount kit
- 860661736-MV2-C03 Dual Samsung 320W mount kit
- 860661736-MV2-C07 Nokia AZHL & APAM PSU

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Mid pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Non-tapered poles   Tapered poles   Wood poles
<b>Power Supply Compatibility</b>	ABB CC1600   APAM   CCI PSU-1200W-48-N   DELTA 2.0   DELTA 3.0   PSU-AC-08

# SSC-760249586X1 | Radio Enclosure MV2

---

<b>Radio Compatibility, Ericsson</b>	220x   440x   4415   4426   4449   4455   4478   8843   8863
<b>Radio Compatibility, Nokia</b>	AHBCA   AHBCC   AHFIA   AHFIB   AHFIC   AHLBA   AHLBBA   AWHQN   AZHL
<b>Radio Compatibility Samsung</b>	RF4402D-D1A   RFV01U-D1A   RFV01U-D2A   RT2201-46A   RT4401-48A
<b>Radios Included</b>	None

## Dimensions

<b>Height</b>	1,219.2 mm   48 in
<b>Width</b>	609.6 mm   24 in
<b>Depth</b>	635 mm   25 in

## Electrical Specifications

<b>Power/Fiber Input</b>	Trade size knockouts at rear side
--------------------------	-----------------------------------

## Material Specifications

<b>Finish Aluminum</b>	Chromate
<b>Finish Concealment Covers</b>	Powder coated
<b>Material Type</b>	Aluminum   Steel

## Environmental Specifications

<b>Thermal Compliance</b>	GR-487
---------------------------	--------

## Packaging and Weights

<b>Volume</b>	0.49 m <sup>3</sup>   17.3 ft <sup>3</sup>
<b>Weight (loaded)</b>	215.456 kg   475 lb
<b>Weight (unloaded)</b>	31.751 kg   70 lb

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--