

# 760248969 | 360G2-iP-32-MPO-SD-KIT-1PK



## SYSTIMAX 360™ iPatch® 32-MPO Sliding Shelf, 1PK imVision Upgrade Kit

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Upgrade kit
<b>Product Brand</b>	LazrSPEED®   SYSTIMAX 360™   iPatch®

### General Specifications

<b>Color</b>	Cool gray
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface</b>	MPO

### Dimensions

<b>Height</b>	26.162 mm   1.03 in
<b>Width</b>	194.31 mm   7.65 in
<b>Depth</b>	17.78 mm   0.7 in

### Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)
----------------------	--

### Optical Specifications

<b>Fiber Mode</b>	Multimode   Singlemode
-------------------	------------------------

### Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	Austel   CE   CSA   UL

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 0.113 kg | 0.25 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

