

CT-460-100



Cable Tie, Heat Stabilized, Weather-resistant, 460 mm length, 100 pcs

Product Classification

Product Type	Cable tie
Ordering Note	CommScope® standard product in the United States and Canada

General Specifications

Accessories	Adapters
Color	Black
Hanger Type	Cable tie
Mounting	Angle member Cable ladder Round member

Dimensions

Height	1.778 mm 0.07 in
Width	7.112 mm 0.28 in
Length	0.46 m 1.51 ft
Compatible Diameter, maximum	127 mm 5 in
Compatible Diameter, minimum	4.775 mm 0.188 in

Material Specifications

Material Type	Heat-stabilized weather resistant nylon
----------------------	---

Mechanical Specifications

Tensile Force	533.786 N 120 lbf
----------------------	---------------------

Environmental Specifications

Operating Temperature	-60 °C to +115 °C (-76 °F to +239 °F)
------------------------------	---------------------------------------

Packaging and Weights

Packaging quantity	100
---------------------------	-----

CT-460-100

Weight, gross

0.54 kg | 1.19 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

CSA

Compliant

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

