

# MUK-MSK1 | SMALL CROSSOVER PLATE

---



Small Crossover Plate, connects 2-3/8" and 2-7/8" OD Pipes

## Product Classification

**Product Type** Clamp plate

## General Specifications

**Mounting** Crossover plate

## Dimensions

**Mounting Diameter, maximum** 73.025 mm | 2.875 in

**Mounting Diameter, minimum** 60.325 mm | 2.375 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Environmental Specifications

**EPA with 1/2 in (12 mm) radial ice** ft<sup>2</sup>

## Packaging and Weights

**Included** Plates | U-bolts

**Packaging quantity** 1

## \* Footnotes

**EPA with 1/2 in (12 mm) radial ice** EPA—Effective Projected Area