


# NG4-CMD70RG

---



NG4access® Cabled Module, singlemode SC/UPC to stub, 72 fiber, rollable ribbon, indoor/outdoor

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cabled module
<b>Product Brand</b>	NG4access®
<b>Product Series</b>	NG4
<b>Ordering Note</b>	For fiber modules with custom cable lengths, please contact your local CommScope representative

## General Specifications

<b>Configuration Type</b>	NG4 Module to Stub tail
<b>Adapters, quantity, front</b>	72
<b>Body Style</b>	Straight orientation
<b>Cable Color</b>	Black
<b>Cable Type</b>	Indoor/outdoor - Rollable Ribbon
<b>Color, housing</b>	Black
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	Stub tail
<b>Polarity</b>	Pairs, straight
<b>Total Fibers, quantity</b>	72
<b>Total Ports, quantity, front</b>	72

## Dimensions


<b>Height</b>	13.3 mm   0.524 in
---------------	--------------------

# NG4-CMD70RG

**Width** 159.9 mm | 6.295 in

**Depth** 101 mm | 3.976 in

## Ordering Tree



## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A1

## Environmental Specifications

**Operating Temperature** -5 °C to +40 °C (+23 °F to +104 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 85%, non-condensing

## Packaging and Weights

**Packaging quantity** 1

# NG4-CMD70RG

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

