



Propel 1RU sliding tray white fiber panel, accepts Propel ULL modules or adapter packs, providing up to 72 duplex LC ports, 72 MPO ports or 144 SN ports (288f)

- Any size Propel component can be used in each panel or blade
- Components can be installed and removed from front or rear of panel
- Supports 8f, 12f, 16f and 24f applications while maintaining full panel density
- Cable mounting system allows for multiple trunk cables to be securely attached in the rear of panel

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber patch panel
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color</b>	White
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	44 mm   1.732 in
<b>Width</b>	483 mm   19.016 in
<b>Depth</b>	470 mm   18.504 in

## Port Configuration

Panel size	8-fiber components	12-fiber components	16-fiber components	24-fiber components
1RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
2RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
4RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
Each blade has 12 lanes				
	Requires 2 lanes	Requires 3 lanes	Requires 4 lanes	Requires 6 lanes

## Material Specifications

**Material Type** Aluminum | Steel

## Environmental Specifications

**Safety Standard** c-UL-us

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 5.375 kg | 11.85 lb