

# CCA-CORDS

---

## Base Product



## CCA Ceiling connector to RJ45 Cords

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Twisted pair patch cord

## General Specifications

<b>ANSI/TIA Category</b>	6   6A
<b>Cable Type</b>	F/UTP (shielded)   U/UTP (unshielded)
<b>Conductor Type</b>	Solid
<b>Interface, Connector A</b>	Ceiling connector
<b>Interface, Connector B</b>	RJ45 plug
<b>Pairs, quantity</b>	4
<b>Wiring</b>	T568B

## Material Specifications

<b>Contact Plating Material</b>	Precious metals
<b>Material Type</b>	Copper alloy   High-impact, flame retardant, thermoplastic

## Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	750 times
<b>Plug Retention Force, minimum</b>	133 N   29.9 lbf

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing

# CCA-CORDS

---

**Environmental Space** Low Smoke Zero Halogen (LSZH) | Plenum

**Flammability Rating** UL 94 V-0

**Safety Standard** ETL | cETL

## Packaging and Weights

**Packaging quantity** 1