

# A-100461

---

## Base Product

Combiner/ Mast head amplifier enclosure for micro cell sites

- Sealed to outside environment
- Double wall construction

## Product Classification

**Product Type** Micro cell site enclosure

**Ordering Note** For UK region only

## General Specifications

**Access** Front door

**Batteries Supported** 0

**Cabinet Type** Combiner cabinet

**Color** Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

**Door Security** Swing handle with 22mm profile cylinder

**Doors, quantity** 1

**Mounting** Plinth | Root

## Dimensions

**Height** 1524 mm | 60 in

**Width** 762 mm | 30 in

**Depth** 508 mm | 20 in

## Electrical Specifications

**Generator Connection** No connection

**Rectifiers, quantity** 0

## Material Specifications

**Finish** Powder coated

**Material Type** Stainless steel

## Environmental Specifications

# A-100461

---

**Qualification Standards** IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP45

## Packaging and Weights

**Included** Brackets | Installation Kit

**Weight, net** 74.843 kg | 165 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system