A-100468

Base Product



Three Phase Meter Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Power supply enclosure

General Specifications

Access Front door

Accessories Cable plate | In-ground root | Plinth

Batteries Supported

Batteries Supported, with optional battery pedestal 0

Cabinet Type Meter cabinet

Color Green | Green (RAL 6009) | Light Gray (RAL

7035) | Others available at additional cost

Door Security 7 mm triangle lock

Internal Mounting Surface 12 mm plywood backboard

Dimensions

 Height
 1016 mm | 40 in

 Width
 660.4 mm | 26 in

 Depth
 254 mm | 10 in

Depth, without door 254 mm | 10 in

Electrical Specifications

ac Distribution Type 10-way metal enclosure

ac Feeds, Outgoing, quantity 6

Generator Connection No connection

Power PhaseThreeVoltage415 Vac

Material Specifications



A-100468

Finish Powder coated

Material Type Galvanized steel

Packaging and Weights

Weight, net 35.834 kg | 79 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system