## 1168156-ZZ | FL2-R970096A0-0A00-R



FL2000 Fiber Termination Panel, 96 SC/UPC, singlemode, 6RU, 19 in, putty white

#### **Product Classification**

Regional Availability Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber patch panel

Product Series FL2000

General Specifications

**Functionality** Patching

Adapter Packs Included, quantity 8

**Color** Putty white

**Growth Configuration** Fully loaded

Interface, front SC/UPC

Rack Type EIA 19 in

Rack Units 6

Shelf Movement Hinged

Splicing Capacity, maximum 0

Total Ports, quantity 96

**Dimensions** 

 Height
 266.7 mm | 10.5 in


 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Ordering Tree



## 1168156-ZZ | FL2-R970096A0-0A00-R



### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

**Fiber Mode** Singlemode

### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

Packaging and Weights

**Included** Mounting hardware

Packaging quantity

Regulatory Compliance/Certifications



# 1168156-ZZ | FL2-R970096A0-0A00-R

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

