

# TFP-1LAQ5-020B

---

TFP Fiber Termination Panel, 48 LC/UPC, singlemode, 1RU, 19 in, black

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Regional Availability</b> | Latin America   North America |
| <b>Portfolio</b>             | CommScope®                    |
| <b>Product Type</b>          | Fiber patch panel             |
| <b>Product Series</b>        | TFP                           |

## General Specifications

|                                  |                                      |
|----------------------------------|--------------------------------------|
| <b>Functionality</b>             | Patching   Splicing                  |
| <b>Body Style</b>                | Symmetrical                          |
| <b>Color</b>                     | Black                                |
| <b>Color, front</b>              | Black                                |
| <b>Interface, front</b>          | LC/UPC                               |
| <b>Patch Cord Entry Location</b> | Front, left side   Front, right side |
| <b>Rack Type</b>                 | EIA 19 in   EIA 23 in                |
| <b>Rack Units</b>                | 1                                    |
| <b>Shelf Movement</b>            | Sliding                              |
| <b>Total Ports, quantity</b>     | 48                                   |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 44.45 mm   1.75 in   |
| <b>Width</b>  | 482.6 mm   19 in     |
| <b>Depth</b>  | 399.29 mm   15.72 in |

## Ordering Tree

# TFP-1LAQ5-020B

TFP - X X AP X X X X X

## Number of Fiber Ports

|    |   |
|----|---|
| 12 | 12 fiber ports: 6 LC adapters;<br>6 SC duplex adapters;<br>12 ST adapters |
| 24 | 24 fiber ports: 12 LC adapters  |

## Pack Orientation

|   |             |
|---|-------------|
| L | angle left  |
| R | angle right |

## Adapter Style

| Multimode Connectors  |                       |
|-----------------------|-----------------------|
| C3                    | SC duplex (beige)     |
| C4                    | SC duplex (aqua)      |
| Q1                    | LC (beige)            |
| Q2                    | LC (aqua)             |
| T1                    | ST®                   |
| Singlemode Connectors |                       |
| C8                    | SC UPC duplex (blue)  |
| A2                    | SC APC duplex (green) |
| Q5                    | LC UPC (blue)         |
| T2                    | ST UPC                |

## Pigtail Length

|       |                  |
|-------|------------------|
| Leave | Adapters only    |
| Blank | Adapters only    |
| 3     | 3 meter pigtails |

## Pigtail Type

|       |                     |
|-------|---------------------|
| Leave | Adapters only       |
| Blank | Adapters only       |
| B     | Singlemode stranded |
| E     | Multimode stranded  |

## Fiber Size

|       |                          |
|-------|--------------------------|
| Leave | Adapters only            |
| Blank | Adapters only            |
| B     | OM1 - 62.5/125 Multimode |
| D     | OM3 - 50/125 LOMMF 300m  |
| S     | Singlemode               |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -40 °C to +85 °C (-40 °F to +185 °F) |
| <b>Storage Temperature</b>   | -40 °C to +85 °C (-40 °F to +185 °F) |

## Packaging and Weights

|                           |                     |
|---------------------------|---------------------|
| <b>Included</b>           | Mounting hardware   |
| <b>Packaging quantity</b> | 1                   |
| <b>Weight, net</b>        | 4.649 kg   10.25 lb |

## Regulatory Compliance/Certifications

# TFP-1LAQ5-020B

---

**Agency****Classification**

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

