

760104307 | M4800-1U-PS



M4800 1U Modular Panel, 48 port (MPS100 / UNJ600 / UNJ600T / UNJ500), Black

- Available for use with the DYMO® labeling solution

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Series	M Series

General Specifications

ANSI/TIA Category	5e 6
Color	Black
Intelligence Type	Passive
Rack Type	EIA 19 in
Rack Units	1
Total Ports, quantity	48

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	53.85 mm 2.12 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Steel
----------------------	-----------------------------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

760104307 | M4800-1U-PS

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

