760109744 | M4800A-1U-GS



M4800 1U Angled Modular Panel, 48 port (MGS600 / MGS400 / UNJ10GT), Black

• Available for use with the DYMO® labeling solution

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Product Brand

CommScope®

RJ45 patch panel

GigaSPEED X10D®

Product Series M Series

General Specifications

ANSI/TIA Category 6 | 6A

Color Black
Intelligence Type Passive

Panel Style Angled

Rack Type EIA 19 in

Rack Units 1

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 143 mm | 5.63 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

COMMSCOPE®

760109744 | M4800A-1U-GS

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

