PFP-SPS-Cl



SPS DC Rectifier controller, factory set to 57VDC

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Product Type Controller module

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 19.05 mm | 0.75 in

 Depth
 203.2 mm | 8 in

Electrical Specifications

Input Voltage, nominal -57 Vdc
Electrical Safety Standard UL

Electromagnetic Compatibility/Interference (EMC/EMI) EN 55022 Class A

Environmental Specifications

Standards Compliance EN 61000-4-2 level 4

Packaging and Weights

Packaging quantity 1

Packaging Type Carton

Weight, net 0.227 kg | 0.5 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

PFP-SPS-Cl

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant





