

# TFAH-ES70/80/50-17



ION®-B Series High Power Remote Unit for LMR 700, LMR 800 and UHF Band High Power Applications

## Product Classification

<b>Product Type</b>	Remote unit
<b>Product Brand</b>	ION®-B

## General Specifications

<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Class</b>	High

## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>License Band</b>	LMR 700   LMR 800   UHF
<b>Voltage Range</b>	85 to 265 Vac

## Electrical Specifications, Rx (Uplink)

<b>Operating Frequency Band</b>	406 – 512 MHz (UHF)   788 – 806 MHz (LMR 700)   806 – 824 MHz (LMR 800)
---------------------------------	---

## Electrical Specifications, Tx (Downlink)

<b>Operating Frequency Band</b>	406 – 512 MHz (UHF)   758 – 775 MHz (LMR 700)   851 – 869 MHz (LMR 800)
---------------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



