

19256B-C

Lace-up Hoisting Grip with tie wraps for HELIAX® cables



Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	431.8 mm 17 in
Leader Length, minimum	330.2 mm 13 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	226.796 kg 500 lb
---------------------------	---------------------

Packaging and Weights

19256B-C

Height, packed	38.1 mm 1.5 in
Width, packed	218.44 mm 8.6 in
Length, packed	220.98 mm 8.7 in
Packaging quantity	1
Weight, gross	0.22 kg 0.485 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

