

243095-2



Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Double Click-on Hangers, includes 3/8 in bolts and hardware, 247.65 mm (9.75 in) length

Product Classification

| | |
|----------------------|--------------------------------------|
| Product Type | Hardware kit |
| Ordering Note | CommScope® standard product (Global) |

General Specifications

| | |
|--------------------|--------|
| Thread Size | 3/8 in |
|--------------------|--------|

Dimensions

| | |
|-----------------------------|---------------------|
| Maximum Stack Height | 3 |
| Length | 247.65 mm 9.75 in |
| Nominal Size | 1-1/4 in 1-5/8 in |

Material Specifications

| | |
|----------------------|-----------------|
| Material Type | Stainless steel |
|----------------------|-----------------|

Packaging and Weights

| | |
|---------------------------|--|
| Height, packed | 254 mm 10 in |
| Width, packed | 88.9 mm 3.5 in |
| Length, packed | 88.9 mm 3.5 in |
| Included | Forty flat washers Forty lock washers Ten 3/8 in threaded rods Twenty hex nuts |
| Packaging quantity | 10 |
| Weight, gross | 1.361 kg 3 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power