

## Cold shrink Kit for 7/8 in to 1/4 in through 1/2 in connections



## Product Classification

<b>Product Type</b>	Cold shrink kit
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Application</b>	Provides additional moisture seal for cable connections
<b>Applications per Kit</b>	One 1/4 in–1/2 in to 7/8 in
<b>Cable Family</b>	AL5-50   AVA5-50   ETS1-50T   FSJ1-50B   FSJ1-75   FSJ4-50B   FSJ4-75A   LDF1-50   LDF4-50A   LDF4-75   LDF5-50A   LDF5-75   VXL5-50
<b>Color</b>	Black

## Dimensions

<b>Width</b>	53.848 mm   2.12 in
<b>Length</b>	254 mm   10 in
<b>Cable Diameter for Seal, maximum</b>	21.34 mm   0.84 in
<b>Cable Diameter for Seal, minimum</b>	7.37 mm   0.29 in
<b>Inner Diameter</b>	51.31 mm   2.02 in
<b>Nominal Size</b>	1/2 in   1/4 in   7/8 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance Test Method</b>	UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
----------------------------------	--

# 245171

---

<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.6.0   MIL-STD-1344A, Method 1002
<b>Packaging and Weights</b>	
<b>Height, packed</b>	299.72 mm   11.8 in
<b>Width, packed</b>	71.12 mm   2.8 in
<b>Length, packed</b>	45.72 mm   1.8 in
<b>Included</b>	One EPDM rubber tube   One sealing foam strip
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.18 kg   0.397 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

