



## Single Entrance Panel for elliptical waveguide 77

### Product Classification

**Product Type** Entrance panel

### General Specifications

**Color** Gray  
**Entry Panel Port Size** 101.6 mm | 4 in  
**Number of Ports** 1  
**Panel Type** Single

### Dimensions

**Height** 76.2 mm | 3 in  
**Width** 127 mm | 5 in  
**Waveguide Size** WR112 | WG15 | R84

### Material Specifications

**Material Type** Aluminum

### Environmental Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

### Packaging and Weights

**Height, packed** 180.34 mm | 7.1 in  
**Width, packed** 180.34 mm | 7.1 in  
**Length, packed** 180.34 mm | 7.1 in  
**Included** Boot | Plate  
**Packaging quantity** 1  
**Weight, gross** 0.91 kg | 2.006 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

- 204673-1 – One 4" Port Entrance Panel 1 x 1
- WGB4-77 – Boot Assembly, 4 in, for elliptical waveguide  
77