

# DLX-SCA-CONV-25

---

## DLX to SC/APC Converter



- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Fiber converter
<b>Product Brand</b>	DLX®
<b>Product Series</b>	FHD

## General Specifications

<b>Interface, Connector A</b>	Hardened mini-size DLX
<b>Interface, Connector B</b>	SC/APC

## Optical Specifications

<b>Insertion Loss, maximum</b>	0.5 dB
<b>Return Loss, minimum</b>	65 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Qualification Standards</b>	Telcordia GR-326-CORE

## Packaging and Weights

<b>Packaging quantity</b>	25
---------------------------	----

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

# DLX-SCA-CONV-25

---

