

SSH-78



SnapStak® Hanger for 7/8 in coaxial cable

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	CommScope® standard product (Global)

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	40.9 mm 1.61 in
Width	40.1 mm 1.579 in
Length	64 mm 2.52 in
Compatible Cable Diameter Range	26.7–31 mm
Compatible Diameter, maximum	31 mm 1.22 in
Compatible Diameter, minimum	26.7 mm 1.051 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

SSH-78

Material Type Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 15.6 cm | 6.142 in

Width, packed 14.8 cm | 5.827 in

Length, packed 10.8 cm | 4.252 in

Packaging quantity 10

Weight, gross 0.42 kg | 0.926 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power