SSC-760236577N2 | 18 in Pole Top for Nokia or Samsung



Top of Pole 18in Dia Concealment Enclosure for up to three Nokia Metro Cell radios Or Samsung LAA/CBRS

- Enclosure for holding up to 3 Nokia metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

- -Supports AWHQN with separately available kit "860665079-AMK-001"
- -Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Product Classification

Portfolio CommScope®

Product Type Pole top

Product Brand Metro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Antenna Compatibility, CommScope Canister Antennas

Antenna Compatibility, Other Vendors ACE | AMPHENOL | GALTRONICS | GAMMA

NU | JMA | KATHREIN | KMW | ROSENBERGER

Antennas Included None

Color Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Brown (RAL 8014) | Faux

Concrete | Green (RAL 6005) | Metallic Silver | White (RAL 9010)

Cooling Passive Cooling

Mounting Options Non-tapered poles | Tapered poles | Wood poles

Radio Compatibility, Nokia (3) Airscale micro radios (Including LAA & CBRS

models) | AHFB | AHIA | AHIB | AWHQN | AZRB | Airscale

micro | Diplexer | Power Distribution

Radio Compatibility Samsung

Diplexer | Power Distribution | RT2201-46A | RT4401-48A

COMMSCOPE®

SSC-760236577N2 | 18 in Pole Top for Nokia or Samsung

Radios Included None

Dimensions

 Height
 812.8 mm | 32 in

 Width
 457.2 mm | 18 in

 Depth
 457.2 mm | 18 in

Mounting Bolt Circle Diameter 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

 Volume
 0.134 m³ | 4.72 ft³

 Weight (unloaded)
 34.019 kg | 75 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

