



FDC Fiber access terminal for aerial applications, 5 mm drop cable rubber sealing, no Adapters, 72 fusion splices

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   Middle East/Africa   North America
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Series</b>	FDC

## General Specifications

<b>Cable Ports Quantity, total</b>	4 round ports + 8 round ports
<b>Cable Sealing Type</b>	Compressed rubber
<b>Closure Sealing Type</b>	Hinged with latch   Hinged with latch, bolts and rubber H seal
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Facade   Strand   Wall
<b>Port Type</b>	No adapter   No adapters
<b>Port, quantity</b>	8
<b>Splice Tray Included, quantity</b>	3
<b>Splice Tray Type Included</b>	24-way, heat shrink
<b>Splitter Type</b>	No splitter
<b>Splitter, quantity</b>	0

## Dimensions

<b>Height</b>	76.5 mm   3.012 in
<b>Width</b>	237 mm   9.331 in
<b>Length</b>	285 mm   11.22 in
<b>Cable Entry Drop Port Diameter</b>	5 mm   0.197 in
<b>Cable Entry Main Port Diameter</b>	6 mm   0.236 in

# 760252621 | FDC-W8-FAT-AE5-NN-0-NN-72

---

**Main Cable Diameter, maximum** 14 mm | 0.551 in

## Material Specifications

**Material Type** Rugged polymer

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

