

# 760254513 | EPX-3U-SPL-ENC



EPX 3U Splicing Fiber Panel accepts up to 7 EPX splice trays providing up to 336 single fiber splicing or up to 1008 ribbon fiber splicing

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber splice panel  |
| <b>Product Series</b>        | EPX   |

## General Specifications

|                         |          |
|-------------------------|----------|
| <b>Color</b>            | Black    |
| <b>Color, front</b>     | Black    |
| <b>Interface, front</b> | Unloaded |
| <b>Rack Units</b>       | 3        |
| <b>Shelf Movement</b>   | Sliding  |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 177 mm   6.969 in    |
| <b>Width</b>  | 482.6 mm   19 in     |
| <b>Depth</b>  | 434.1 mm   17.091 in |

## Environmental Specifications

|                            |           |
|----------------------------|-----------|
| <b>Flammability Rating</b> | UL 94 V-0 |
|----------------------------|-----------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>   |
|---------------|---|
| CHINA-ROHS    | Below maximum concentration value   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant   |
| UK-ROHS       | Compliant   |

