

LS2-HMHM-6M-W-PB

LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, with HELIAX® SureGuard weatherproofing, with Integrated Birdproofing Shell, 6m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® Premium, static PIM
Product Brand	HELIAX® SureFlex®
Product Series	LSF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	6 m 19.685 ft
Nominal Size	3/8 in

Electrical Specifications

3rd Order IMD	-119 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.065	30
1700–2200 MHz	1.065	30
2200–2700 MHz	1.083	28
3400–3800 MHz	1.222	20

LS2-HMHM-6M-W-PB

3800-6000 MHz

1.222

20

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method

HELIAX® SureGuard weatherproofing boot