

7818454 | Optical Demultiplexer, 4 channels



CWDM Fiber Optical Module, Demux, 1350-1410 nm, LC/PC, 4 channels

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX

General Specifications

Device Type	Plug-in module
Functionality	Demultiplexing

Dimensions

Height	29 mm 1.142 in
Width	130 mm 5.118 in
Depth	185 mm 7.283 in

Packaging and Weights

Height, packed	65 mm 2.559 in
Width, packed	275 mm 10.827 in
Depth, packed	160 mm 6.299 in
Weight, gross	0.5 kg 1.102 lb
Weight, net	0.4 kg 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant/Exempted

