# 760246159 | OCP-L1-02MASEN-XX-(12COL)



Fiber Optic Pigtail, 12 fibers, Singlemode, LC/UPC to Stub, 0.9 mm diameter, multicolor, 2m

### Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, multi-fiber
Product Series	OCP

### General Specifications


Connector A, quantity	12
Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	LC/UPC
Total Fibers, quantity	12

#### Dimensions

**Cord Length** 

2 m | 6.562 ft

### Ordering Tree



 Standard Configuration by default 900µm buffer buffer color : yellow

250 µm color : natural or milky white

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024



# 760246159 | OCP-L1-02MASEN-XX-(12COL)

### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	G.657.A1, TeraSPEE

G.657.A1, TeraSPEED®

### **Environmental Specifications**

**Environmental Space** 

Low Smoke Zero Halogen (LSZH)

### Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

