


FPS-C1JJBA0BN1-EX



FDH 3000 Plug-and-Play CWDM Module, 4-channel, SC/APC

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	FDH 3000 Mini FDH 3000
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Device Type	Plug-and-play module
Functionality	Demultiplexing Multiplexing
Application	For use in FDH 3000 cabinets
Circuits, quantity	1
Distribution Type	4-channel CWDM
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Interface, rear	SC/APC
Multiplexers, quantity	1

Dimensions

Height	88.9 mm 3.5 in
Width	12.7 mm 0.5 in

FPS-C1JJBA0BN1-EX

Depth 139.7 mm | 5.5 in

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Flammability Rating UL 94 V-0

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE | Telcordia GR-326-CORE

Packaging and Weights

Included Reversible dust cap

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

