

# AT-10-43-MF

---



## 10 dB Coaxial Attenuator DC-6000 4.3-10 M-F

### Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Attenuator

### General Specifications

**Device Type** Attenuator

**Application** Indoor

**Color** Silver

**Inner Contact Plating** Silver

**Interface** 4.3-10 Male

**Interface 2** 4.3-10 Female

**Outer Contact Plating** Trimetal

### Electrical Specifications

**Return Loss, minimum** 20.8 dB

**Attenuation** 10 dB

**Attenuation Tolerance**  $\pm 0.5$  dB

**Average Power, maximum** 2 W

**Impedance** 50 ohm

**Operating Frequency Band** 0 – 6000 MHz

**Peak Power, maximum** 0.5 kW

**VSWR** 1.2

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

### Regulatory Compliance/Certifications

# AT-10-43-MF

---

**Agency**

CHINA-ROHS

ROHS

UK-ROHS



**Classification**

Above maximum concentration value

Compliant/Exempted

Compliant/Exempted