



MMO Type Flush Mounted Angled Faceplate, four port ivory

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Flush mount outlet

General Specifications

Application	Has 45 degree angular ports for fiber and copper connectors
Color	Ivory
Mounting	Flush
Total Ports, quantity	4

Dimensions

Height	144.526 mm 5.69 in
Width	83.312 mm 3.28 in
Depth	32.766 mm 1.29 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
Weight, net	0.159 kg 0.35 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

107655177 | M14MMO-246

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

