

CZ8127-000 | RFP-1-60-S2-1-L-W-TE



RapidFiber® Faceplate, SC/APC, 60 meters cable on spool, wall mount

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Faceplate kit
Product Brand	RapidFiber®
Product Series	RFP

General Specifications

Cover Type	Hinged with latches
Interface Type	SC/APC
Mounting	Wall mount
Port Capacity, maximum	2
Total Ports, quantity	1

Dimensions

Height	74.93 mm 2.95 in
Width	115.062 mm 4.53 in
Depth	52.07 mm 2.05 in
Cable Length	60 m 196.85 ft
Cable Diameter	1 mm 0.039 in

Material Specifications

Material Type	LSZH thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.B3

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

