

LS2-XMHM-6M-P



LSF2-50 SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male, 6m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	LSF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	NEX10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	6 m 19.685 ft
Nominal Size	3/8 in

Electrical Specifications

3rd Order IMD	-116 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.065	30.04
1700–2200 MHz	1.083	27.99
2500–2700 MHz	1.106	25.96
3400–3800 MHz	1.222	20.01

LS2-XMHM-6M-P

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ROHS

Classification

Above maximum concentration value

Compliant/Exempted



Included Products

- | | | |
|---------|---|--|
| LS2XM-P | - | NEX10 Male for 3/8 in LSF2-50 cable, factory attached |
| LSF2-50 | - | LSF2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket (Not for Individual Sale - Jumpers only) |
| P4HM-S2 | - | 4.3-10 Male for 3/8 in LSF2-50 cable, factory attached |