

# 760248942



Kit, SMB, 1 Fiber Port, 1 Power Port, Black

Powered Fiber Cable Surface Mount Box Kit, 1 Fiber Port, 1 Power Port, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Surface mount module
<b>Product Series</b>	SL Series   SLX Series

## General Specifications

<b>Application</b>	Powered fiber
<b>Color</b>	Black
<b>Interface Feature, front</b>	Fiber LC Duplex (1)   Open SL Ports (2)   Two wire terminals (1)
<b>Mounting</b>	Surface
<b>Outlet Orientation</b>	Flat
<b>Port Marking Type</b>	Label
<b>Total Ports, quantity</b>	4

## Dimensions

<b>Height</b>	38 mm   1.496 in
<b>Width</b>	142.3 mm   5.602 in
<b>Depth</b>	116.2 mm   4.575 in

## Electrical Specifications

<b>Input Power</b>	100 W (NEC Class 2)
<b>Input Voltage</b>	30 Vac   60 Vdc
<b>Electrical Safety Standard</b>	CB   IEC 60950-1   IEC 62368-1   UL   cUL

## Material Specifications

<b>Material Type</b>	Polycarbonate
----------------------	---------------

## Environmental Specifications

# 760248942

---

**Environmental Space** Indoor  
**Flammability Rating** UL 94 V-0

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 0.141 kg | 0.31 lb