

# 1316MCLICK



Miniature Click-on Hanger for 13–16 mm cable - Hardware Sold Separately

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Click-on hanger
<b>Mounting</b>	M8 through hole

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	38.1 mm   1.5 in
<b>Width</b>	24.9 mm   0.98 in
<b>Length</b>	55.1 mm   2.169 in
<b>Compatible Cable Diameter Range</b>	13–16 mm
<b>Compatible Diameter, maximum</b>	16.3 mm   0.642 in
<b>Compatible Diameter, minimum</b>	13.7 mm   0.539 in
<b>Nominal Size</b>	1/2 in   3/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

## Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

# 1316MCLICK

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	44.7 cm   17.598 in
<b>Width, packed</b>	39.4 cm   15.512 in
<b>Length, packed</b>	17.7 cm   6.969 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.05 kg   0.11 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power