

# ST-BSP30

---



## Ballast Pole, 30 ft

- Bolt-together ballast tray foundation
- No digging required
- Removable step pegs
- Collar mounting

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Monopole
<b>Ordering Note</b>	CommScope® non-standard product
<b>Warranty</b>	One year

## General Specifications

<b>Application</b>	Multi-point telecommunications   Point-to-point communications
<b>Equipment Load Rating</b>	18 in microwave reflector   Omni antenna   Telecommunications unit
<b>Foundation</b>	Non-penetrating above ground design with aggregate fill
<b>Monopole Capability Type</b>	Medium duty
<b>Monopole Design</b>	Round conical
<b>Optional Accessories</b>	Antenna mounts   Cabinet mounts   Removable step pegs   Solar mounts

## Dimensions

<b>Height</b>	9.144 m   30 ft
<b>Mounting Diameter, maximum</b>	266.7 mm   10.5 in
<b>Mounting Diameter, minimum</b>	160.02 mm   6.3 in
<b>Base Area</b>	8 ft x 8 ft

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating Test Method</b>	TIA/EIA-222-G
--------------------------------	---------------

# ST-BSP30

---

## Packaging and Weights

<b>Included</b>	Ballast tray   Ground tab   Hand holes   Lightning rod   Monopole   Safety climb systems   Safety-climb   Step pegs
<b>Packaging quantity</b>	1
<b>Weight, net</b>	306.3 kg   675.275 lb

### \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines