

ST-DBH60



Double Hinged Pole, 60 ft

- Hoist-operated, counterbalanced hinged design
- No climbing necessary for equipment installation
- Single person service
- Rivet nut mounting
- Secure locking

Product Classification

Product Type Monopole

General Specifications

Application Positive train control/Centralized traffic control (PTC/CTC communications)

Equipment Load Rating 2 ft microwave reflector | Solar panel | Telecommunications unit

Foundation Base

Monopole Capability Type Heavy duty

Monopole Design Round conical

Optional Accessories Antenna mounts | Cabinet mounts | Hoist | Solar mounts

Dimensions

Height 18.288 m | 60 ft

Mounting Diameter, maximum 342.9 mm | 13.5 in

Mounting Diameter, minimum 200.66 mm | 7.9 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs

Packaging quantity 1

Weight, net 910.8 kg | 2,007.968 lb