

HCDO-2BDDLOA



EHD-2U Pre-stubbed Patch Panel with LC Adapter and 288f I/O, Riser /LSZH rollable ribbon cable, left cable entry, singlemode with cable length in meters from 25m to 400m in 25m increments

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	EHD

General Specifications

Color	Black
Interface Feature, front	LC
Interface Feature, rear	Stub
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity, front	288

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	465.84 mm 18.34 in
Cable Stub Length	100 m 328.084 ft 125 m 410.105 ft 150 m 492.126 ft 175 m 574.147 ft 200 m 656.168 ft 225 m 738.189 ft 25 m 82.021 ft 250 m 820.21 ft 275 m 902.231 ft 300 m 984.252 ft 325 m 1,066.273 ft 350 m 1,148.294 ft 375 m 1,230.315 ft 400 m 1,312.336 ft 50 m 164.042 ft 75 m 246.063 ft

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2 OS2

HCDO-2BDDLOA

Insertion Loss, maximum 0.35 dB

Included Products

- | | | |
|--|---|--|
| 760239308
N-288-CN-RR-F12YL/8G1/99G
/C | - | Indoor, All-Dielectric, Low Smoke Zero Halogen (LSZH), Riser-Rated, Gel-Free, Central Tube Rollable Ribbon Cable |
| 760245230
N-192-CN-RR-F12YL/8G1/99G
/C | - | Indoor, All-Dielectric, Low Smoke Zero Halogen (LSZH), Riser-Rated, Gel-Free, Central Tube Rollable Ribbon Cable |