

# CM-30S-B

---



## Chain Mount Base Kit, 14 in stand-off, 8 ft chain

### Product Classification

**Product Type** Chain mount kit

### General Specifications

**Chains, quantity** 2

**Pipe, quantity** 0

**Sectors, quantity** 1

### Dimensions

**Height** 152.4 mm | 6 in

**Width** 203.2 mm | 8 in

**Length** 203.2 mm | 8 in

**Chain Length** 2,400.3 mm | 94.5 in

**Mounting Diameter, maximum** 762 mm | 30 in

**Mounting Diameter, minimum** 203.2 mm | 8 in


**Pipe Outer Diameter** 60.96 mm | 2.4 in

**Mounting Circumference, maximum** 2,392.68 mm | 94.2 in

**Mounting Circumference, minimum** 635 mm | 25 in

# CM-30S-B

## Outline Drawing



## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL

**Wind Rating Criteria** One 96 in x 10 in panel antenna per sector

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Brackets | Chains | Hardware

# CM-30S-B

---

**Packaging quantity** 1  
**Weight, net** 31.8 kg | 70.107 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code