FPX-12MPLS0J



FPX Fiber Optic MPO Module, Singlemode OS2, 12 fiber SC/APC adapter, left, putty white

- FPX modules offer the end-user the flexibility of a plug-and-play MPO architecture with a "grow as you go" approach to the network
- Each module has a front bulkhead identical to the adapter pack with an internal cable assembly converting to an MPO male connector
- All fiber connectivity is housed in an enclosed module with a rear MPO adapter allowing the user to utilize an MPO trunk to turn up service

Product Classification

North America **Regional Availability Portfolio** CommScope® **Product Type** Fiber module

Product Series FPX

General Specifications

Functionality Breakout

For use with FPX panels **Application**

Adapter Color Green Adapters, quantity, front 12

Adapters, quantity, rear

Body Style Left orientation | Simplex

Color, front Putty white Putty white Color, housing Color, rear Putty white Interface, front SC/APC Interface, rear MPO

Interface Feature, rear APC

Polarity Pairs, straight

Total Ports, quantity, front 12

Dimensions

Height 33.02 mm | 1.3 in


COMMSCOPE®

FPX-12MPLS0J

Width 176.53 mm | 6.95 in

Depth 127 mm | 5 in

Ordering Tree



Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

Insertion Loss, maximum0.25 dBReturn Loss, minimum65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

FPX-12MPLS0J

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

TL 9000:2016 (R6) Compliant to this quality management practice

UK-ROHS Compliant

