


# RCP-172DU006100

---



RapidFiber® Termination Panel, 24-Position 1RU, singlemode, SC/UPC to stub, 61 m

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel, with rapid cable
<b>Product Brand</b>	RapidFiber®
<b>Product Series</b>	RCP

## General Specifications

<b>Functionality</b>	Patching
<b>Body Style</b>	Symmetrical
<b>Cable Exit Location</b>	Rear, left side
<b>Cable Stub Type</b>	Indoor/outdoor, microcable
<b>Color</b>	Putty white
<b>Door Type, front</b>	Hinged   Slide latch   Transparent
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	Stub tail
<b>Patch Cord Entry Location</b>	Front, left side   Front, right side
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Total Fibers, quantity</b>	24
<b>Total Ports, quantity</b>	24
<b>Transmission Standards</b>	IEC 60794-2   ISO/IEC 11801   TIA/EIA-568-B.3


## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in

# RCP-172DU006100

**Depth** 381 mm | 15 in  
**Cable Length** 61 m | 200.131 ft

## Ordering Tree



## Material Specifications

**Finish** Powder coated  
**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode  
**Fiber Type** G.652.D | G.657.A2/B2

# RCP-172DU006100

---

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +55 °C (+23 °F to +131 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–85%, non-condensing
<b>Qualification Standards</b>	NEBS Level 3   Telcordia GR-1435   Telcordia GR-326   Telcordia GR-409   UL 1863

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

