

760168419 | 360G2-iP-1U-96F-LC-DP-SD



SYSTIMAX 360™ iPatch® G2 1U 96F-LC Distribution Panel, Sliding Panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Brand	LazrSPEED® SYSTIMAX 360™ iPatch®

General Specifications

Color	Black
Intelligence Type	iPatch® enabled
Interface, front	LC/UPC
Rack Units	1
Shelf Movement	Sliding
Total Ports, quantity	48

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	478.79 mm 18.85 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

760168419 | 360G2-iP-1U-96F-LC-DP-SD

Safety Standard Austel | CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 2.948 kg | 6.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

