760231506 | HD-1U-SP



High Density 1U Sliding fiber Splice Panel, accepts (4) G2 modules, providing up to 48 duplex LC ports, accepts splice wallets, RoloSplice trays and stackable splice trays

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series HD

General Specifications

Color Black + Silver gray (front)

Intelligence Type iPatch® ready

Interface, front Unloaded

Rack Type EIA 19 in

Rack Units 1

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 450.85 mm | 17.75 in

 Depth
 505.46 mm | 19.9 in

Material Specifications

Material Type Steel

Environmental Specifications

Safety Standard UL 1863

Packaging and Weights

Packaging quantity 1

Page 1 of 2

760231506 | HD-1U-SP

Weight, net 5.375 kg | 11.85 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

