# 760245728 | CHD12-DM-12LC-WB-B-ULL



CHD ULL Multimode MPO-12 distribution module, 12LC to 1x12f MPO unpinned, dust plugs

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber moduleProduct BrandSYSTIMAX ULL

Product Series CHD

## General Specifications

Functionality Breakout

Color, front Lime green

Color, rearGrayInterface, frontLC/UPCInterface, rearMPO

Interface Feature, rear Key up/up | MPO Non-Pinned

Polarity Method B Enhanced (ULL)

Shuttered No Total Fibers, quantity 12

#### **Dimensions**

 Height
 12.45 mm | 0.49 in

 Width
 83.82 mm | 3.3 in

 Depth
 131.83 mm | 5.19 in

### **Optical Specifications**

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED® wideband

**Insertion Loss, maximum** 0.35 dB

**COMMSCOPE®** 

# 760245728 | CHD12-DM-12LC-WB-B-ULL

## **Environmental Specifications**

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

## Packaging and Weights

Packaging quantity 1

**Weight, net** 0.082 kg | 0.18 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

